

SERIE SS-ZD

Gauze Swab Folding Machine (folded edge)



Series gauze swab folding machine can do customize to meet most of the gauze swab folding methods, sizes and plies request, such like folded edge or un-folded edge, with or without X-ray thread, 5x5cm, 7.5x7.5, 10x10cm, 8x18cm, 7.5x10cm,10x20cm, 4ply, 8ply, 12ply, 16ply, etc.

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



WUHAN LOYAL MACHINERY CO., LTD



SERIE SS-ZD

Gauze Swab Folding Machine (folded edge)

TECHNICAL SPECIFICATIONS



The heating roll can on-line perm (melt) the PVC X-ray thread on the gauze fabric. (PVC X-ray thread material cost is much lower than weaved X-ray thread.)

Humidification and iron system makes the gauze swab folding in very good shape.





The output tracks from 1-6 lanes which will customized according gauze swab folding method and size request.

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.





SERIE SS-ZD

Gauze Swab Folding Machine (folded edge)



Via simple adjustment, different tier (4ply, 8ply, 12ply and 16ply) can be done in ONE machine.

Technical Parameter	
Folding speed	42-52 pieces/lane/min
Output tracks	1-2 lanes
Main power	1.1KW
Heating power	2.8KW
Compressor air	0.3-0.5Mpa

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.

