



# SERIE SS-SBQ

*Gauze / Non-woven Ball Making Machine*



Machine is developed to automatically making gauze (or non-woven) balls.

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



**WUHAN LOYAL MACHINERY CO., LTD**

© 3-502, Chutian 181 Cultural Creative Industry Park, Donghu Road No. 181,  
Wuchang District, 430000, Wuhan City, Hubei Province, China

Mobile: 0086 1387 1887 978 Tel / Fax: 0086 27 8566 3380

E-mail: [loyal@med-machinery.cn](mailto:loyal@med-machinery.cn) [michelle\\_6237@hotmail.com](mailto:michelle_6237@hotmail.com)


[www.med-machinery.cn](http://www.med-machinery.cn)



# SERIE SS-SBQ


*Gauze / Non-woven Ball Making Machine*

## TECHNICAL SPECIFICATIONS



Automatically unwind the gauze (or non-woven) material roll, cutting the fabric at fixed size, feeding the rubber pipe and cut the pipe as an small size elastic rubber ring. The folding system will make the gauze (or non-woven) material incorporate into the rubber elastic ring, following series of folding and winding steps, a gauze (or non-woven) ball been making done.

Gauze ball diameter change within 1cm range can via parameter setting to achieve.



Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



**WUHAN LOYAL MACHINERY CO., LTD**

©3-502, Chutian 181 Cultural Creative Industry Park, Donghu Road No. 181,  
Wuchang District, 430000, Wuhan City, Hubei Province, China

Mobile: 0086 1387 1887 978 Tel / Fax: 0086 27 8566 3380

E-mail: [loyal@med-machinery.cn](mailto:loyal@med-machinery.cn) [michelle\\_6237@hotmail.com](mailto:michelle_6237@hotmail.com)

[www.med-machinery.cn](http://www.med-machinery.cn)



# SERIE SS-SBQ

*Gauze / Non-woven Ball Making Machine*



Feeding gauze or non-woven material with X-ray thread, the finally product can with X-ray.

## Technical Parameter

Capacity	30 balls/min
Gauze ball diameter range	1.8-2.5cm, 2.5-3.5cm, 3.5-4.5cm, 4.5-5.5cm (Accept customize)
Operator request	1 person can operate 3-4 sets of machine

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



**WUHAN LOYAL MACHINERY CO., LTD**

© 3-502, Chutian 181 Cultural Creative Industry Park, Donghu Road No. 181,  
Wuchang District, 430000, Wuhan City, Hubei Province, China

Mobile: 0086 1387 1887 978 Tel / Fax: 0086 27 8566 3380

E-mail: loyal@med-machinery.cn michelle\_6237@hotmail.com

www.med-machinery.cn